Max Connectivity, Mini Footprint

Process Weighing in Hazardous Areas



Weigh

The IND131xx and IND331xx terminals deliver excellent accuracy, reliability and efficiency for process weighing applications in hazardous areas.



Comply

These superior weighing terminals feature the performance and reliability expected of instruments designed to comply with Weights & Measures, hazardous area and product safety regulations. They include features and functionality never before offered in such a compact and versatile form factor.



Control

The inherent qualities of process weighing terminals from METTLER TOLEDO make it easier for OEMs and system integrators to build best-in-class weighing systems cost-effectively.



Connect

Easy integration into process-based network architectures provides valuable plant-floor information to process owners to optimize production and reduce down-time.



DeviceNet >





Multiple PLC interfaces

All IND131xx and IND331xx terminals can be equipped with any of a wide array of PLC options.

Zone 2/22, Division 2



IND131xx and IND331xx Weighing Terminals

The IND131xx and IND331xx analog scale terminals deliver precision measurement data in a single, cost-effective package, safe for use in Zone 2/22 and Division 2/Zone 2 hazardous areas. Terminal features include:

- Organic LED display readable in all light conditions
- Ultra-fast A/D conversion rate and TraxDSP® digital filtering
- Enclosures designed to match application environment – modular design enables multiple mounting possibilities
- 24 VDC operation
- Support for a wide variety of options, including DIO, additional serial port, and PLC interfaces
- Portable calibration/configuration settings and firmware update via an SD memory card
- Scale calibration through PLC interface. CalFREE[®]
 allows scales to be calibrated without test weights



IND131xx / IND331xx Packaged Solutions Enhanced Terminals in Robust Enclosures

- Packaged IND131xx and IND331xx in Enclosures Approved for Division 2, Zone 2 and Zone 22
- Each version can be configured with any of the terminals' multiple interface and connectivity options
- Packages include an agency-approved
 24 VDC power supply

Enclosure Specifications

The stainless steel enclosure housing the IND131xx DIN and IND331xx panel packaged solutions is FM-approved for use in safe areas, and in Division 2, Zone 2 hazardous areas. The enclosure is ATEX/IECEx certified for Zone 22 (dust) hazardous areas. Cable entry points can be either conduit hubs for use in the U.S., or ATEX-approved glands for European applications.

- FM-certified enclosure, gas and dust
- ATEX and IECEx certified for Zone 2/22 environments
- Rated IP66, IP65 when used with panel-mount terminal
- T5 temperature class rating





Multiple Terminal Configurations Available

When a single terminal is not enough, multi-terminal designs are available, with agency-approved power supply, optional ISB (Intrinsically Safe Barrier) and additional features as required for the application.

Load Cells in Hazardous Areas

In applications with load cells installed in Division 1/Zone 1 or Zone 1/21 areas, an intrinsically safe analog load cell barrier (ISB) is required. IND131xx and IND331xx terminals packaged with a METTLER TOLEDO ISB05 intrinsically safe barrier provide an integrated solution for such applications. Refer to the control drawing for load cell compatibility.



| Table | FM-approved conduit hubs | ATEX-approved glands Single /Dual terminal | |
|-------------|--------------------------|--|--|
| Terminal | Single /Dual terminal | | |
| IND131xx | Standard* | Standard* | |
| DIN-mount | with ISB05(s) | with ISBO5(s) | |
| IND331xx | Standard* | Standard* | |
| Panel-mount | with ISB05(s) | with ISB05(s) | |
| | | | |

^{*} Terminal with agency-approved 24VDC power supply

Packaged Model Configurations

IND131xx and IND331xx packages are highly customizable. **Table** shows the array of available primary configurations.

Two possible variants are illustrated below. **Figure 1** shows a system comprising an IND131xx with optional ISB05 barrier. **Figure 2** shows an IND331xx panelmount terminal (its front panel interface not shown). The packaged model configurations are available with any of the PLC interfaces (EtherNet/IP, PROFIBUS DP, Modbus TCP, Allen-Bradley RIO, ControlNet, Device-Net), and Solid State DIO.



Figure 1



Figure 2

IND131xx-based package

- ISB05 (optional)
- FM/CSA/ATEX approved power supply, 24VDC at 1.3 A, 100-240 VAC, 50/60 Hz
- ATEX glands (for European installations)
- FM, ATEX and IECEx- certified enclosure

IND331xx-based standard package

(front panel display not shown)

- FM/CSA/ATEX approved power supply, 24VDC at 1.3 A, 100-240 VAC, 50/60 Hz
- Conduit hubs (for installation in US/Canada)
- FM, ATEX and IECEx-certified enclosure



The packaged IND131xx and IND331xx can be customized for specific uses, to include agency-approved operators for I/O, such as annunciators and pushbuttons, making operator interactions even easier, more consistent and safer.



IND131xx and IND331xx Weighing Terminals

| Technical Data | | | IND131xx DIN mounted | IND331xx Panel mounted | IND131xx JBox enclosure |
|------------------------------|-------------------------|---|--|--|--|
| | | | | 1111 000 | |
| Enclosure types | | Unit of Measure | DIN rail-mount, plastic, with operator interface | Panel mount, stainless steel with operator interface + plastic chassis | Stainless steel enclosure including internal board to sum load cells |
| Dimensions | L×H×D | mm in. | 68 × 138 × 111 2.7 × 5.4 × 4.4 | Front panel: 168 × 68 × 12 6.6 × 2.7 × 0.5 | 251 × 261 × 123 9.9 × 10.3 × 4.8 |
| Shipping weight | | kg / lb | 1 / 2.2 | 1.5 / 3.3 | 5.5 / 12.1 |
| Environmental protection | | | IP20, Type 1 | IP65, Type 4x and 12 | IP69k |
| A selection of the second | Operation | °C / °F | -10 to 40 / 14 to 104, 10% to 90% relative humidity, non-condensing | | ty, non-condensing |
| Ambient environment | Storage | °C / °F | -20 to 60 / -4 to 140, 10 % to 90 % relative humidity, non-condensing | | |
| Power requirements | | VDC / mA | 18-36; nominal 24 / 84-170; nominal 120 (IND131xx), nominal 130 (IND331xx) | | nominal 130 (IND331xx) |
| Display | Туре | | Green OLED including weight display, weight units, gross/net indication and graphic symbols for motion and center of zero. 10 updates/sec. | | et indication dates/sec. |
| . , | Character height | mm / in. | 5.6 / 0.22 | 12 / 0.47 | 5.6 / 0.22 (internal) |
| Weight display | | | Maximum displayed resolution of 100,000 divisions | | |
| Scale type | | | | Analog load cells | |
| Number of cells | | | Up to 4 350 Ω load cells, 2 or 3 mV/V | | |
| Number of scales | | | | 1 | |
| Analog/Digital update rates | | Hz | Internal analog: 366 / Target comparison: 50 / PLC Interface: 20 | | |
| Digital Filtering | | | TraxDSP® | | |
| Memory | | | Stores two-speed target control values and limit values for three comparators | | |
| Applications | | | Basic process weighing for gain-in-weight (filling), loss-in-weight (dosing) and level indication | | |
| Load cell excitation voltage | | VDC | 5 | | |
| μV Build Minimum/Approved | | microvolts | 0.1 / 0.6 | | |
| Keypad | | | 4 keys (Clear, Zero, Tare, Print); 1.22mm thick polyester overlay (PET) with polycarbonate display lens | | |
| Oceaninications | Serial interfaces | | Standard: One serial port (COM1), RS-232, 300 to 115,200 baud Optional: Serial port (COM2), RS-232/485, 300 to 115,200 baud | | |
| Communications | Protocol | | Serial inputs: ASCII commands for CTPZ (Clear, Tare, Print, Zero), SICS (most commands, levels 0 and 1) Serial outputs: Continuous, Extended continuous, or Demand (limited formats) | | |
| | Weights and Measures | | USA: NTEP Class III/IIIL - 10,000d; CoC 09-051 | | Europe: OIML, Class III, 6000e; R76/2006-NL1-09.26 |
| Approvals | Hazardous locations | USA - FM NI / I, II, III / 2 / ABCDEFG / T5 Ta I / 2 / IIC / T5 Ta = | 40°C / T5 Ta = 40°C | ATEX EX II 3 G Ex nA nL [nL] IIC T5 Ex nA nL [nL] II 3 D Ex tD A22 IP 65 T Ex tD A22 IP 100°C Ex tD A22 IP | 65 T100°C |
| | | Install per | Control Drawing 72238303R | Install per Installation Drawing 72246 | |
| | MID | | OIML R51 (Automatic Catchweighing) T10262; OIML R61 (Automatic Gravimetric Weighing) T10261 | | |
| | Product Safety | | UL, cUL, CE | | |

Options

| - p | | | | |
|---|--------------------------------------|--------------------------|--|--|
| COM2 / DIO, includes: | COM2 RS-232/485 serial | Modbus RTU capability | | |
| | 4 solid state discrete outputs | 2 discrete inputs (selec | 2 discrete inputs (selectable active or passive) | |
| Programmable Logic Control (PLC) interfaces | 4-20 mA Analog Output | Ethernet/IP™* | DeviceNet™ | |
| | PROFIBUS® DP | Modbus TCP | | |
| | Allen-Bradley RIO™ | Control | ControlNet™* | |
| * Class 1 Cyclic and Class 3 Dis | crete / Explicit messaging supported | | | |



IND331 with PTPN adapter plate

| Accessories | Agency-approved (FM/CSA/ATEX) 24VDC DIN rail mount Power Supply | PTPN Terminal adapter plate (for IND331 Panel unit) | |
|-------------|---|---|--|
| | ISB05 Intrinsically Safe Barrier when Load Cells | 2GB Memory SD Card for configuration | |
| | are in Zone 1/21 or Div 1 areas | and calibration data backup and restore | |

USA

Mettler-Toledo, LLC 1900 Polaris Parkway Columbus, OH, 43240 Tel. (1) 800 523 5123 Canada

Mettler-Toledo, Inc. 2915 Argentia Road, Unit 6 Mississauga, Ontario, L5N 8G6 Tel. (1) 800 523 5123 www.mt.com

For more information

Subject to technical changes © 06/2013 Mettler-Toledo AG Printed in Switzerland MarCom Switzerland





